

Digital Dry Block Heater Series

Dry block heaters for incubation up to 150 °C. Select the heater and interchangeable block for the tube diameter or plate format.



Technical Information

Temperature range	ambient +5-150 °C
Heating time	≤30 min; 20-150 °C
Temperature stability at 40 °C	±0.3 °C
Temperature stability at 100 °C	±0.5 °C
Temperature stability at 120 °C	±1 °C
Display resolution	0.1 °C
Power variants	200 / 400 / 600 W
Dimensions	260 × 220 × 100 / 260 × 220 × 95 / 360 × 220 × 100 mm

Interchangeable block options

Block	Tube diameter / volume	Positions	Dimensions (mm)
D1	6 mm	48	96.5 × 76.5 × 50
D2	7 mm	48	96.5 × 76.5 × 50
D3	10 mm	24	96.5 × 76.5 × 50

Interchangeable block options			
Block	Tube diameter / volume	Positions	Dimensions (mm)
D4	12 mm	24	96.5 × 76.5 × 50
D5	13 mm	24	96.5 × 76.5 × 50
D6	15 mm	12	96.5 × 76.5 × 50
D7	16 mm	12	96.5 × 76.5 × 50
D8	19 mm	12	96.5 × 76.5 × 50
D9	20 mm	12	96.5 × 76.5 × 50
D10	26 mm	8	96.5 × 76.5 × 50
D11	28 mm	6	96.5 × 76.5 × 50
D12	40 mm	3	96.5 × 76.5 × 50
D13	0.2 mL	48	96.5 × 76.5 × 50
D14	0.5 mL	48	96.5 × 76.5 × 50
D15	1.5 mL	24	96.5 × 76.5 × 50
D16	2.0 mL	24	96.5 × 76.5 × 50
D17	0.2 mL	96	96.5 × 153 × 33.5
D18	flat plate	96-well plate	96.5 × 153 × 22.5
D19	custom	-	-

Standard Configuration

The quotation must identify the selected instrument configuration and supplied accessories. Where several specifications are listed, they describe separate versions in the same order; they do not describe one combined configuration.

Optional Configuration

Optional equipment and consumables are supplied only when itemized in the quotation. Confirm dimensions, compatibility, electrical supply and the required configuration before ordering.

Selection and ordering

Include the PRECETTA model, selected specification, sample or application, quantity and destination in your inquiry. Use the complete PDF to compare variants and configuration details.

Technical Information

Select the heater power and block independently. The block table lists compatible formats, not an included set of every block. The supplied block quantity must be itemized; custom blocks require confirmation.